

Garant
Solid carbide milling cutter TPC, TiAlN, Ø f8 DC: 20mm

Order data

Order number	203077 20
GTIN	4045197657305
Item class	11X

Description
Version:

High-performance slot drill for machining materials up to 60 HRC, **specially designed for TPC applications.**

Strengthened core. With corner radii similar to torus cutters.

Note:

h_{max} : The values stated in the table are maximum values.

$a_{e_{max}} = 0.05 \times D$ for TPC machining.

Technical description

Recess Ø D_1	19.8 mm
Cutting edge Ø D_c	20 mm
No. of teeth Z	5
Overhang length L_1 incl. recess	70 mm
Average chip thickness h_{max} for TPC milling in steel < 60 HRC	0.062 mm
Shank Ø D_s	20 mm
Overall length L	126 mm
Flute length L_c	60 mm
Direction of infeed	horizontal and oblique
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	f8

Balance quality with shank	G 2.5 with HB
Helix angle	45 degrees
Corner rounding r_v	0.3 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.05 \times D$
Through-coolant	no
Machining strategy	TPC
Colour ring	red
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	150 m/min	P
Steel < 50 HRC	suitable	140 m/min	H
Steel < 55 HRC	suitable	125 m/min	H
Steel < 60 HRC	suitable	110 m/min	H
dry	Suitable only under restricted conditions		
Air	suitable		