

Mitutoyo**External blade micrometer, Measuring range: 0-25mm****Order data**

Order number	421896 0-25
GTIN	4946368847313
Item class	44A

Description**Version:**

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Spindle Ø	6.35 mm
Calibration	B1
Scale divisions	0.01 mm
Flat blade anvils width	0.75 mm
Measuring range	0 - 25 mm
Spindle pitch	0.5 mm
Flat blade anvils length	6.5 mm
Micrometer barrel graduations	1/50 mm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box

Type of product

External micrometer

ServicesCalibration External micrometer without setting dimension
maximum measuring range 25 mm

022000 25

DAkkS calibration External micrometer without setting
dimension maximum measuring range 100 mm

022010 100