

Mitutoyo**External blade micrometer, Measuring range: 75-100mm****Order data**

Order number	421896 75-100
GTIN	4946368847344
Item class	44A

Description**Version:**

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Flat blade anvils length	6.5 mm
Spindle pitch	0.5 mm
Measuring range	75 - 100 mm
Flat blade anvils width	0.75 mm
Spindle Ø	6.35 mm
Micrometer barrel graduations	1/50 mm
Calibration	B2
Scale divisions	0.01 mm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100