




Self-centring 4-jaw lathe chuck ROTA-M-flex 2+2, External diameter: 630mm



Order data

Order number	313101 630
GTIN	2050002052987
Item class	33U

Description

Version:

The 4-jaw manual chuck combines the advantages and functions of 2-, 3- and 4-jaw chucks and is extremely flexible for use on lathes, milling machines and milling-turning centres. The opposing jaw pairs are connected using a drive ring system, meaning the workpieces are centrally clamped and a pivot mechanism prevents them from being over-defined. A compensating mechanism also enables thin-walled workpieces to be clamped centrally. For stationary applications, the clamping set-up must be provided using console (base) or adapter plates.

- **Clamping of round and cubic workpieces and workpieces with an awkward geometric shape.**
- **Sealed design – thus also suitable for castings and forgings.**
- **Visual indicator pin for ensuring process reliability when clamping the component.**
- **Can also be used as a 2-jaw chuck.**

Standard:

ISO 702-4

Supplied with:

T-nuts/fastening screws and clamping wrench.

Note:

Clamping jaws are not included. Available on request.

Technical description

maximum speed	950 min ⁻¹
Weight	307 kg
Series	ROTA-M flex
External Ø A	630 mm
maximum clamping force	180 kN
maximum torque	250 Nm
Compensating stroke per jaw	10 mm
Clamping stroke per jaw	17.8 mm
Number of jaws	4
Operation	manual
Type of product	Self-centring chucks