



## Cantilever arm rack KRM, double-sided, Depth 2×800 mm, Rack height / rack width: 2500/800mm



### Order data

|              |                 |
|--------------|-----------------|
| Order number | 991653 2500/800 |
| GTIN         | 4052941991479   |
| Item class   | 95S             |

### Description

#### Version:

Cantilever arm rack for provision of material and storage of pipes, sections and long, bulky materials. Cantilever arms are inserted and can be adjusted without further aids. Base profiles made from angled sections for even distribution of the load. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

Load capacities apply to each side of the stiles, where the cantilever arms are evenly divided over the height.

#### Supplied with:

2 cantilever arm stiles, 2 longitudinal braces, 1 pc. cross brace including fastenings, safe working load sign. See table for number of cantilever arms.

#### Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

#### Note:

- **Floor and wall fastenings are not included.**
- **Delivered unassembled.**
- **Load capacities apply to evenly distributed loads.**

Type of installation: Plug-in racking

Load capacity per cantilever arm: 180 kg

Rack height: 2500 mm

Rack width: 800 mm  
Number of cantilever arms double-sided: 16  
Load capacity per stand: 1000 kg

## Technical description

|  |                        |
|--|------------------------|
| Rack access                            | double-sided           |
| Application range                      | Cantilever arm racking |
| Number of cantilever arms double-sided | 16                     |
| Height                                 | 2500 mm                |
| Rack height                            | 2500 mm                |
| Customer assembly                      | yes                    |
| Number of levels                       | 8                      |
| Rack width                             | 800 mm                 |
| Width                                  | 800 mm                 |
| Load capacity per stand                | 1000 kg                |
| Series                                 | KRM                    |
| Height adjustment interval             | 50 mm                  |
| Type of installation                   | Plug-in racking        |
| Product name attribute                 | Depth 2×800 mm         |
| Load capacity per cantilever arm       | 180 kg                 |
| Type of product                        | Cantilever arm racking |