

**Milling cutter lock screw through bored, DIN 6367, for mandrel Ø: 50mm****Order data**

Order number	309861 50
GTIN	4250122681601
Item class	30N

Description**Application:**

For attaching shell-type milling cutters.

Coolant supply via lateral holes.

Note:

Compatible with

- **Interface HSK, PSC.**
- **Interface SK and BT only with arbor form ADB.**

Technical description

Thread M	M24
Thread length	36 mm
Head thickness	12 mm
for mandrel Ø	50 mm
Head Ø	63 mm
Standard	DIN 6367

Type of product

Tightening screw