

**2-component adhesive, Manufacturer ID: DP100PLUS****Order data**

Order number	083374 DP100PLUS
GTIN	638060089767
Item class	08M

**Description****Version:**

**Tough resilient 2-component adhesive** for quick and easy jointing, makes a permanent joint. Cures at room temperature.

**Application:**

Use manual application gun No. 083373 size PISTOLE together with delivery piston No. 083375 size KOLBEN3 and mixing tubes No. 083383 size MIXER.

**Technical description**

Touch dry after	20 min
Working life after date of manufacture	20 mo
Storage temperature	16 - 25 °C
Capacity	50 g
Operating temperature range	-55 - 80 °C
Tensile shear strength	7 N/mm <sup>2</sup>

Density	1.15 g/cm <sup>3</sup>
Chemical basis	Epoxy resin
hazardous goods class	9
Labelling of hazardous substances	GHS09: Environment
Labelling of hazardous substances	GHS07: Exclamation mark
Functional strength to	2880 min
UN number	UN3082
Colour	transparent
Dynamic viscosity	19000 mPas
Manufacturer's designation	DP100 PLUS
Shape	liquid
Suitable for material	Aluminium
Suitable for material	Glass
Suitable for material	wood
Suitable for material	Steel
Suitable for material	Plastic
Resistant to impacts and vibrations	no
Lap shear strength	24 N/mm <sup>2</sup>
Type of product	Two-component adhesive