




Double-ended ring spanner set, cranked, Number of tools: 8



Order data

Order number	952445 8
GTIN	4062406573089
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 952445: 1 pc.

GARANT double-ended ring spanner deep cranked no. 615950 size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22: 1 pc. each

Technical description

Depth in G	20
Width in G	8
Depth	500 mm
Number of tools	8
Width	200 mm
Weight	1.316 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×20
Type of product	Rigid foam inlay

Accessories

Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615950 8X9
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615950 12X13
Double-ended ring spanner, deeply cranked Width across flats 19X22 mm	615950 19X22
Double-ended ring spanner, deeply cranked Width across flats 18X21 mm	615950 18X21
Double-ended ring spanner, deeply cranked Width across flats 6X7 mm	615950 6X7
Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615950 16X17
Rigid foam inlay for tool sets suitable for rigid foam set 952445	952001 952445
Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615950 10X11
Double-ended ring spanner, deeply cranked Width across flats 14X15 mm	615950 14X15