

Garant
End mill HSS-Co8, uncoated, Ø k10 DC: 32mm

Order data

Order number	191500 32
GTIN	4045197103079
Item class	11W

Description
Version:

Multi-flute end mill. **Eccentric relief ground.**
Centre cutting edge geometry for plunging.

Technical description

No. of teeth Z	6
Feed f_z for slot milling in steel < 750 N/mm ²	0.05 mm
Cutting edge Ø D_c	32 mm
Shank Ø D_s	32 mm
Overall length L	133 mm
Flute length L_c	53 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 1835 B to h6
Tolerance nominal Ø	k10
Helix angle	30-40 degrees
Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	HSS Co 8
Standard	DIN 844 B

Type	N
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	83 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	25 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	25 m/min	P
GG(G)	suitable only under restricted conditions	23 m/min	K
CuZn	suitable only under restricted conditions	55 m/min	N
Uni	suitable		
wet maximum	suitable		