



## Cantilever arm rack KRM, double-sided, Depth 2x800 mm, Rack height / rack width: 3000/800mm



### Order data

Order number	991653 3000/800
GTIN	4052941991509
Item class	95S

### Description

#### Version:

Cantilever arm rack for provision of material and storage of pipes, sections and long, bulky materials. Cantilever arms are inserted and can be adjusted without further aids. Base profiles made from angled sections for even distribution of the load. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

Load capacities apply to each side of the stiles, where the cantilever arms are evenly divided over the height.

#### Supplied with:

2 cantilever arm stiles, 2 longitudinal braces, 1 pc. cross brace including fastenings, safe working load sign. See table for number of cantilever arms.

#### Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

#### Note:

- **Floor and wall fastenings are not included.**
- **Delivered unassembled.**
- **Load capacities apply to evenly distributed loads.**

Type of installation: Plug-in racking

Load capacity per cantilever arm: 180 kg

Rack height: 3000 mm

Rack width: 800 mm

Number of cantilever arms double-sided: 16

Load capacity per stand: 950 kg

## Technical description

Number of levels	8
Customer assembly	yes
Application range	Cantilever arm racking
Rack height	3000 mm
Height	3000 mm
Width	800 mm
Rack access	double-sided
Rack width	800 mm
Number of cantilever arms double-sided	16
Load capacity per stand	950 kg
Series	KRM
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Product name attribute	Depth 2x800 mm
Load capacity per cantilever arm	180 kg
Type of product	Cantilever arm racking