



Cantilever arm rack KRM, double-sided, Depth 2×800 mm, Rack height / rack width: 2500/1000mm



Order data

Order number	991653 2500/1000
GTIN	4052941991493
Item class	95S

Description

Version:

Cantilever arm rack for provision of material and storage of pipes, sections and long, bulky materials. Cantilever arms are inserted and can be adjusted without further aids. Base profiles made from angled sections for even distribution of the load. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

Load capacities apply to each side of the stiles, where the cantilever arms are evenly divided over the height.

Supplied with:

2 cantilever arm stiles, 2 longitudinal braces, 1 pc. cross brace including fastenings, safe working load sign. See table for number of cantilever arms.

Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

Note:

- **Floor and wall fastenings are not included.**
- **Delivered unassembled.**
- **Load capacities apply to evenly distributed loads.**

Type of installation: Plug-in racking

Load capacity per cantilever arm: 180 kg

Rack height: 2500 mm

Rack width: 1000 mm
Number of cantilever arms double-sided: 16
Load capacity per stand: 1000 kg

Technical description

Rack height	2500 mm
Application range	Cantilever arm racking
Rack access	double-sided
Height	2500 mm
Customer assembly	yes
Number of levels	8
Rack width	1000 mm
Number of cantilever arms double-sided	16
Width	1000 mm
Load capacity per stand	1000 kg
Series	KRM
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Product name attribute	Depth 2×800 mm
Load capacity per cantilever arm	180 kg
Type of product	Cantilever arm racking