

Garant
Burr set GARANT Master Uni – medium, 5 pieces, Carbide, Number of burrs: 5

Order data

Order number	541405 5
GTIN	4062406587062
Item class	51D

Description
Version:

Multi Cut carbide burr set with popular shape variants.

The newly developed innovative tooth geometry permits a **high metal removal rate** and at the same time **extremely smooth running and very good guidance**. The optimum chip formation (no pointed chips) achieves high surface quality in roughing and finishing applications.

- **High rate of material removal.**
- **Smooth running.**
- **Low thermal stress, long tool life, improved chip evacuation.**
- **For general-purpose use on steel, stainless steel, aluminium.**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Supplied with:

1 pc. each No. 540220 size A0616, C0616, D0807; G0618; M1020.

Note:

Materials with poor heat conductivity; reduce speed to avoid overheating of the burr and smearing.

Technical description

Series	GARANT Master Uni
Tool material	Carbide
Shank Ø	6 mm
Number of burrs	5
Type of product	Burr

Accessories

BurrGARANT Master Uni – medium Type D0807	540220 D0807
BurrGARANT Master Uni – medium Type C0616	540220 C0616
BurrGARANT Master Uni – medium Type M1020	540220 M1020
BurrGARANT Master Uni – medium Type G0618	540220 G0618
BurrGARANT Master Uni – medium Type A0616	540220 A0616