



## Digital base unit, thread "Go" / "No Go" plug gauge WMCD MultiCheck Digital, For thread M: 12-20



### Order data

Order number	486511 12-20
GTIN	4046122634453
Item class	48B

### Description

#### Version:

MultiCheck Digital base unit with interchangeable gauge inserts, measuring sleeve and protective sleeve for checking the conformity to gauge and measuring thread depths. Measuring depth of up to  $4 \times D$ , max. 80 mm.

#### Advantage:

Testing of various thread sizes using a single base unit. Checking the thread gauge conformity and the thread depth in a single operation. Time saved for one inspection task up to 50%. Easy replacement of worn "Go" / "No Go" gauges.

#### Suitable for:

Thread size: M12; M14; M16; M18; M20

#### Supplied with:

WMCD MultiCheck Digital base unit incl. battery CR2032.

### Technical description

rechargeable	no
Power supply	Battery-powered
Series	Multi-check thread gauge
Scale divisions	0.01 mm
Calibration	Price on request

Test certificate	Manufacturer's test certificate
Battery type	Button cell
Nominal voltage	3 V
International size	CR2032
Number of batteries contained	1
Weight	530 g
Length	247 mm
Diameter	35 mm
Length (assembled)	329 mm
Type of product	Pug Gauge

---

## Accessories

Assembly wrench for MultiCheck Digital For threads 2-20	486513 2-20
---	-------------