

## Garant

### GARANT Master Steel MICRO solid carbide pilot drill, plain shank DIN 6535 HA 5xD, AlCrN, Ø DC: 1,6mm



#### Order data

Order number	121223 1,6
GTIN	4062406579968
Item class	10F

#### Description

##### Version:

**High-performance micro-drill** for general-purpose use on material, focussing on steel processing. Maximum process reliability due to **exactly matched tools within the overall system** and **expanded guide chamfer**. Drilling of very small diameters down to the maximum depth after creating a pilot hole. **Optimum compromise between core diameter and flute size for optimum chip evacuation** – even with long-chipping materials. The **increased metal removal rates and longer tool life** ensure an economical drilling process, even with very small hole diameters combined with a large L/D ratio.

##### Note:

For reliable use of the micro-drills from 8xD, a **pilot hole of at least 4xD** is required using the micro-pilot drill 121223. For vertical machining and flat workpiece surfaces, a pilot hole can be dispensed with from  $D_c = \varnothing 1 \text{ mm}$  up to a length of 12xD. Please always ensure that the **pilot hole is free from chips** before using the subsequent drilling tool. We recommend setting a 90° counterbore with a suitable NC spotting drill after the pilot hole has been completed. For critical applications (e.g. highest possible production accuracy, minimal burr formation, reduced coolant pressure), reduce the feed rate of the tool by 50% before entering and exiting the material. Long-chipping materials may require **chips to be evacuated** in steps of 3xD each by moving the drill back slightly at pilot hole depth. Please make sure that you use a suitable **tool clamping device** (shrink-fit chuck, hydraulic clamping chuck) with a radial run-out of less than 0.003 mm, a sufficiently high **coolant pressure** (at least 30 bar), as well as sufficiently fine **filtration** of the cooling medium ( $D_c < \varnothing 2 \text{ mm}$  with filter  $\leq 0.010 \text{ mm}$ ;  $D_c < \varnothing 3 \text{ mm}$  filter  $\leq 0.020 \text{ mm}$ ). The specified L/D ratio gives the **minimum achievable depth of hole** with the respective micro-drill. Flute length  $L_c = L_2 + 1.5 \times D_c$ .

#### Technical description

Overall length L	44 mm
recommended maximum drilling depth L <sub>2</sub>	8.8 mm
Tolerance nominal Ø	m6
Number of cutting edges Z	2
Flute length L <sub>c</sub>	11.2 mm
Feed f in steel < 1100 N/mm <sup>2</sup>	0.07 mm/rev.
Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.04 mm/rev.
Nominal Ø D <sub>c</sub>	1.6 mm
Shank Ø D <sub>s</sub>	3 mm
Standard	Manufacturer's standard
Series	Master Steel
Coating	AlCrN
Tool material	Solid carbide
Version	5×D
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 40 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	50 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 750 N/mm <sup>2</sup>	suitable	80 m/min	P

Steel < 900 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	Suitable	50 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	50 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	35 m/min	M
Ti > 850 N/mm <sup>2</sup>	Suitable	25 m/min	S
GG(G)	suitable	70 m/min	K
CuZn	suitable only under restricted conditions	50 m/min	N
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		