

**Safety helmet EVO® VISTAlens® Dualswitch™, Colour: WHITE****Order data**

Order number	097861 WHITE
GTIN	5038428409827
Item class	09W

Description**Version:**

The safety helmet combines the EVO® Vista® integrated retractable eye protection with the innovative Dualswitch™ chin strap system. Chin strap trigger force has been designed to comply with both EN397 and EN12492. The integrated retractable eye protection has multiple coatings to protection against UV radiation, scratching and fogging. The adjustable swivel arms allow for easy retraction and extension of the eye protection from the helmet as required. The compact EPP (expanded polypropylene) shell on the inside offers side impact protection acc. to EN12492 and optimises helmet breathability. The helmet can also be used for electrical work thanks to the EN50365 approval.

- **6-point strap.**
- **30 mm Euro slot mounting.**
- **Sweatband made of PU-coated cotton.**
- **With rotary catch.**
- **Reflector elements for improved visibility.**

Application:

Industrial, construction, assembly, outdoor und underground, electrical work.

Standard:

EN397, EN12492, EN50365, EN166, EN170

Technical description

Size	53 - 64 cm
Lens coating	scratch-resistant
Lens coating	scratch-resistant
Weight	580 g
Width adjustment	Drejelukning
Colour	white
Lens material	Polycarbonate
Lens identification	2C-1.2 JSP 1 FTKN
Helmet characteristics	Protection against lateral deformation
Helmet characteristics	Protection against liquid metal spraying out
Helmet characteristics	Electrical insulation
Helmet characteristics	Safety characteristics down to -30 °C
Material of helmet shell	ABS
Standard	DIN EN 12492
Standard	DIN EN 50365
Standard	DIN EN 397
Type of product	Safety helmet

Accessories

Chinstrap Type 2P	097843 2P
EVO® neck protector Colour GREY	097834 GREY