


Solid carbide end mill, TiAlN, Ø h10 DC: 16mm

Order data

Order number	203240 16
GTIN	4045197119032
Item class	12X

Description
Version:

Strengthened core and geometry for hard machining, without dynamic helical pitch.

Application:

For profile milling as finishing.

(Plunge cutting only to shallow depths).

Technical description

Feed f_z for side milling in steel < 55 HRC	0.05 mm
No. of teeth Z	8
Cutting edge Ø D_c	16 mm
Shank Ø D_s	16 mm
Overall length L	92 mm
Flute length L_c	32 mm
Direction of infeed	horizontal and oblique
Shank	DIN 6535 HA to h6
Tolerance nominal Ø	h10
Helix angle	50 degrees
Corner chamfer angle	90 degrees
Coating	TiAlN
Tool material	Solid carbide

Standard	DIN 6527
Type	H
Cutting width a_e for milling operation	$0.05 \times D$ for side milling
Through-coolant	no
Colour ring	red
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable	160 m/min	P
Steel < 1100 N/mm ²	suitable	95 m/min	P
Steel < 1400 N/mm ²	suitable	85 m/min	P
Steel < 50 HRC	suitable	75 m/min	H
Steel < 55 HRC	suitable	65 m/min	H
Steel < 60 HRC	suitable	50 m/min	H
Steel < 65 HRC	suitable only under restricted conditions	30 m/min	H
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------