



Digital base unit, thread "Go" / "No Go" plug gauge WMCD MultiCheck Digital, For thread M: 2-10



Order data

Order number	486511 2-10
GTIN	4046122634446
Item class	48B

Description

Version:

MultiCheck Digital base unit with interchangeable gauge inserts, measuring sleeve and protective sleeve for checking the conformity to gauge and measuring thread depths. Measuring depth of up to $4 \times D$, max. 80 mm.

Advantage:

Testing of various thread sizes using a single base unit. Checking the thread gauge conformity and the thread depth in a single operation. Time saved for one inspection task up to 50%. Easy replacement of worn "Go" / "No Go" gauges.

Suitable for:

Thread size: M2; M3; M4; M5; M6; M8; M10

Supplied with:

WMCD MultiCheck Digital base unit incl. battery CR2032.

Technical description

Calibration	Price on request
Series	Multi-check thread gauge
rechargeable	no
Power supply	Battery-powered
Scale divisions	0.01 mm

Battery type	Button cell
International size	CR2032
Nominal voltage	3 V
Test certificate	Manufacturer's test certificate
Number of batteries contained	1
Weight	250 g
Length (assembled)	233 mm
Length	181 mm
Diameter	28 mm
Type of product	Pug Gauge

Accessories

Assembly wrench for MultiCheck Digital For threads 2-20	486513 2-20
---	-------------