

**Garant**
**Solid carbide forward / reverse deburring tool, TiAlN, Ø DC: 7,8mm**

**Order data**

Order number	208180 7,8
GTIN	4045197465481
Item class	11X

**Description**
**Version:**
**Extra long shank.**

Double ground head **with 45° angle.**

**Application:**

For **forward** and **reverse deburring** and **chamfering** even where access is difficult.

Particularly suitable for **contouring applications.**

**Technical description**

Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.012 mm
Cutting edge Ø D <sub>c</sub>	7.8 mm
L <sub>2</sub> +0.5	2 mm
No. of teeth Z	4
Shape	flat
L <sub>4</sub> +0.5	98 mm
Shank Ø D <sub>s</sub>	6 mm
Overall length L	100 mm
Corner chamfer angle	45 degrees
Chamfer mill	backwards and forwards 45
Coating	TiAlN
Tool material	Solid carbide

Standard	Manufacturer's standard
Type	N
Tolerance nominal $\varnothing$	$\pm 0.05$
Countersink tip angle	90 degrees
Cutting width $a_e$ for milling operation	$0.25 \times L_2$ for side milling
Shank	DIN 6535 HA to h6
Shank tolerance	h6
Colour ring	without
Type of product	Deburrers

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable	115 m/min	N
Alu > 10% Si	suitable	70 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	M
GG(G)	suitable	40 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

### Services

Shank grinding Type HB

129100 HB