

## Garant

### Solid carbide reaming head HPC H7 stainless steel Through hole, TiAlN, Nominal Ø D: 22,201-Xmm



#### Order data

Order number	239730 22,201-X
GTIN	4062406606602
Item class	23A

#### Description

##### Version:

Interchangeable head reamer system **finish ground for fit IT7**. Cutter geometry matched to the application.

**System concentricity  $\leq 5 \mu\text{m}$  (depending on the head and holder) when mounted.**

With short flutes and left-hand helix.

##### Application:

**For through holes.**

For HPC/HSC reaming.

##### Note:

**Total usable length** =  $L_1$  (arbor No. 239740 / 239745) +  $l$  (interchangeable head No. 239710 to 239720).

Suitable assembly wrench No. 219987. Insert for torque wrench No. 219986.

Further sizes available on request. Delivery time: 4 weeks

Minimum order quantity: 1 piece

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned.

#### Technical description

Number of cutting edges Z	8
Arbor size	20 mm

Cutter length $l_1$	14 mm
Head length $l$	26 mm
Ø range	22.201 - 23.2 mm
Series	TopCut
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Hole tolerance	H7
Application for type of drilling	for through holes
Machining strategy	HPC
Through-coolant	yes
Semi-Standard	yes
suitable arbor	GARANT TopCut
Type of product	Cutter insert for reaming

### User data

	Suitability	$V_c$	ISO code
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	25 m/min	M
Oil	suitable		
wet maximum	suitable		