

Deep pot magnet with toleranced dimensions, SmCo₅, Ø: 8mm



Order data

Order number	085928 8
GTIN	2050000964862
Item class	08Q

Description

Version:

- Shielded cylindrical magnets with 3 to 6 times the clamping force of hard ferrite magnets.
- Fit tolerance on the external Ø h6.
- Temperature-resistant up to maximum 200 °C.
- Magnetic core made of samarium-cobalt (SmCo₅).

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

maximum shortening dimension rear	10 mm
Ø	8 mm
Height	20 mm
maximum temperature resistance	200 °C
Material of the surface	Nickel
Nominal clamping force	22 N
Material of the magnet core	SmCo ₅
Type of product	Cylindrical clamping magnet

