

Garant

GARANT Diabolo solid carbide torus cutter HPC, TiAlN, Ø e8 DC / R1: 0,8/0,08mm



Order data

Order number	206162 0,8/0,08
GTIN	4045197597663
Item class	11X

Description

Version:

GARANT Diabolo:

Special geometry, coating and carbide, specially for hard machining.

For copy milling with **angle α : 1° 30'**. Double relief ground side clearance angle.

Tolerances:

- **Corner radius: $R_1 = \pm 0.005$ mm.**
- **Angle $\alpha = \pm 20'$.**

Note:

Standard application values: f_z for $a_p = 0.1 \times D$.

Technical description

Feed f_z for side milling in steel < 65 HRC	0.005 mm
Corner radius R_1	0.08 mm
Recess $\varnothing D_1$	0.75 mm
Feed f_z for copy milling in steel < 65 HRC	0.005 mm
Cutting edge $\varnothing D_c$	0.8 mm
Overhang length L_1 incl. recess	1.6 mm
L_2	27 mm
No. of teeth Z	2
Shank $\varnothing D_s$	3 mm
Flute length L_c	1 mm

Overall length L	75 mm
Shank	DIN 6535 HA to h6
Helix angle	30 degrees
maximum shank recess dia. D_6	2.1 mm
Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	e8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.2×D for side milling
Cutting width a_e for milling operation	0.05×D for copy milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	red
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	180 m/min	P
Steel < 50 HRC	suitable	170 m/min	H
Steel < 55 HRC	suitable	140 m/min	H
Steel < 60 HRC	suitable	135 m/min	H
Steel < 65 HRC	suitable	100 m/min	H
wet maximum	suitable only under restricted conditions		

wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable