

rapid**Hose reel sheet metal reel, Type: 15****Order data**

Order number	080076 15
GTIN	4030704090041
Item class	08A

Description**Version:**

Hose reels with **automatic pull-out and roll-up mechanism guided** by long life steel springs with **multiple stop points per revolution**.

Open hose reel in **painted, partially galvanised sheet steel design** with **variable run-out guide** and robust **rubber hose**.

Application:

Suitable for air, water, oil, diesel.

For increased ergonomics by relieving cable tension, and for ensuring tidiness and for avoiding the risk of accidents and injuries due to hoses lying on the ground.

Technical description

usable hose length	15 m
Connection outlet	1/2 in
maximum operating pressure	50 bar
Connection inlet	1/2 in
Material of the housing	Sheet metal, painted

Body height	494 mm
Body depth	180 mm
Body width	470 mm
Type of product	Hose reel