

Deep pot magnet with toleranced dimensions, SmCo₅, Ø: 10mm



Order data

Order number	085928 10
GTIN	2050000965159
Item class	08Q

Description

Version:

- Shielded cylindrical magnets with 3 to 6 times the clamping force of hard ferrite magnets.
- Fit tolerance on the external Ø h6.
- Temperature-resistant up to maximum 200 °C.
- Magnetic core made of samarium-cobalt (SmCo₅).

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

Material of the surface	Nickel
maximum temperature resistance	200 °C
Ø	10 mm
Nominal clamping force	40 N
Height	20 mm
maximum shortening dimension rear	8 mm
Material of the magnet core	SmCo ₅
Type of product	Cylindrical clamping magnet

