

Garant
**GARANT Master Steel MICRO solid carbide drill, plain shank DIN 6535 HA
12×D, AlCrN, Ø DC h6: 2,51-Xmm**

Order data

| | |
|--------------|---------------|
| Order number | 121226 2,51-X |
| GTIN | 4062406632724 |
| Item class | 10F |

Description
Version:

High-performance micro-drill for universal material use, focussing on steel processing. Maximum process reliability due to **exactly matched tools within the overall system** and **expanded guide chamfers**. Drilling of very small diameters down to the maximum depth after creating a pilot hole. **Optimum compromise between core diameter and flute size for optimum chip evacuation** – even with long-chipping materials. The **increased metal removal rates and longer tool life** ensure an economical drilling process, even with very small hole diameters combined with a large L/D ratio.

Note:

For reliable use of the micro-drills from 8×D, a **pilot hole of at least 4×D** is required using the micro-pilot drill 121223. For vertical machining and flat workpiece surfaces, a pilot hole can be dispensed with from $D_c = \varnothing 1$ mm up to a length of 12×D. Please always ensure that the **pilot hole is free from chips** before using the subsequent drilling tool. We recommend setting a 90° counterbore with a suitable NC spotting drill after the pilot hole has been completed. For critical applications (e.g. highest possible production accuracy, minimal burr formation, reduced coolant pressure), reduce the feed rate of the tool by 50% before entering and exiting the material. Long-chipping materials may require **chips to be evacuated** in steps of 3×D each by moving the drill back slightly at pilot hole depth. Please make sure that you use a suitable **tool clamping device** (shrink-fit chuck, hydraulic clamping chuck) with a radial run-out of less than 0.003 mm, a sufficiently high **coolant pressure** (at least 30 bar), as well as sufficiently fine **filtration** of the cooling medium ($D_c < \varnothing 2$ mm with filter ≤ 0.010 mm; $D_c < \varnothing 3$ mm filter ≤ 0.020 mm). The specified L/D ratio gives the **minimum achievable depth of hole** with the respective micro-drill. Flute length $L_c = L_2 + 1.5 \times D_c$. Delivery time: 10 working weeks

Minimum order quantity: 5 pieces

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over or under deliver by +/-10% (min. 1 pc).

Technical description

| | |
|---------------------------------|-------------------------|
| Tolerance nominal \varnothing | h6 |
| Standard | Manufacturer's standard |
| \varnothing range | 2.51 - 2.6 mm |
| Flute length L_c | 36.4 mm |
| Overall length L | 68 mm |
| Shank $\varnothing D_s$ | 3 mm |
| Number of cutting edges Z | 2 |
| Series | Master Steel |
| Coating | AlCrN |
| Tool material | Solid carbide |
| Version | 12xD |
| Point angle | 128 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Pilot drill required | yes, pilot drill |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|-------------------------------|---|----------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 50 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 50 m/min | N |
| Steel < 750 N/mm ² | suitable | 80 m/min | P |

| | | | |
|--------------------------------|---|----------|---|
| Steel < 900 N/mm ² | suitable | 70 m/min | P |
| Steel < 1100 N/mm ² | suitable | 60 m/min | P |
| Steel < 1400 N/mm ² | Suitable | 50 m/min | P |
| INOX < 900 N/mm ² | suitable | 50 m/min | M |
| INOX > 900 N/mm ² | suitable | 35 m/min | M |
| Ti > 850 N/mm ² | suitable | 25 m/min | S |
| GG(G) | suitable | 70 m/min | K |
| CuZn | suitable only under restricted conditions | 50 m/min | N |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable only under restricted conditions | | |