

Garant**HiPer-Drill cutter insert n7, HU7810, Ø D: 25-Xmm****Order data**

Order number	231630 25-X
GTIN	4062406635756
Item class	20N

Description**Version:**

Vee ground cutter inserts for precise positioning and stable seating.
Concentricity when assembled $\leq 20 \mu\text{m}$. For holes up to IT9 accuracy.

Note:

Cutting data applies for the base body 5xD.

Drill pilot holes exclusively with cutter insert of the same type. Delivery time: 10 working weeks

Minimum order quantity: 3 pieces

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned.

Technical description

Number of changes/inserts	1
Series	HiPer-Drill
Coating	uncoated
for base body size	25 mm

Feed f in aluminium short-chipping	0.46 mm/rev.
Ø range	25 - 25.99 mm
Point angle	135 degrees
Grade	HU7810
Tool material	Carbide
Semi-Standard	yes
Number of cutting edges Z	2
Type of product	Cutter insert for boring

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	250 m/min	N
Aluminium (short chipping)	suitable	200 m/min	N
Alu > 10% Si	suitable	150 m/min	N
CuZn	suitable	180 m/min	N
wet maximum	suitable		