

Garant**HiPer-Drill cutter insert n7, HU7810, Ø D: 11,5-Xmm****Order data**

Order number	231630 11,5-X
GTIN	4062406628888
Item class	20N

Description**Version:**

Vee ground cutter inserts for precise positioning and stable seating.
Concentricity when assembled $\leq 20 \mu\text{m}$. For holes up to IT9 accuracy.

Note:

Cutting data applies for the base body 5xD.

Drill pilot holes exclusively with cutter insert of the same type. Delivery time: 10 working weeks

Minimum order quantity: 3 pieces

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned.

Technical description

Coating	uncoated
Feed f in aluminium short-chipping	0.26 mm/rev.
Series	HiPer-Drill
Number of changes/inserts	1

for base body size	11.5 mm
Ø range	11.5 - 11.99 mm
Point angle	135 degrees
Grade	HU7810
Tool material	Carbide
Semi-Standard	yes
Number of cutting edges Z	2
Type of product	Cutter insert for boring

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	250 m/min	N
Aluminium (short chipping)	suitable	200 m/min	N
Alu > 10% Si	suitable	150 m/min	N
CuZn	suitable	180 m/min	N
wet maximum	suitable		