

Garant
HiPer-Drill base body, 8xD, Ø DC: 47mm

Order data

Order number	231615 47
GTIN	4062406641658
Item class	21S

Description
Version:

- **Very high feed rates and maximum performance due to optimally matched geometries and materials.**
- **Precise positioning of the cutter insert due to Vee insert seating and secure clamping by the centre bore.**
- **High concentricity when assembled.**
- **Shank support for optimum stability in operation.**

Application:

For stationary and rotating use. For holes up to IT9 accuracy.

Recommendation:

Drill the pilot hole.

Note:

Further sizes up to Ø 50.99 mm available on request.

The insert screw must be replaced after every fifth change of cutter insert.

reduce v_f values by 20 %.

Clamp in a hydraulic chuck (such as No. 302026 size 20) for optimum radial run-out.

For optimum stability, clamp the drill so the overhang is as short as possible.

For process reliability when using the drill, initial pilot drilling to 1.5xD with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

Technical description

Overall length L	529 mm
Clamping screw	231999 20IP1 (7.5 Nm)
Series	HiPer-Drill

Dia. range D_c	47 - 48.99 mm
Number of cutting edges Z	2
Shank length L_s	60 mm
Shank $\varnothing D_s$	32 mm
Reach L_1	376 mm
Version	8xD
Shank	ISO 9766
Use for drilling	limited drilling with oblique exit
Use for drilling	limited drilling through a stack
Use for drilling	limited oblique spot drilling
Use for drilling	limited cross-drilling
Through-coolant	yes
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 25IP	674252 25IP
---	-------------