

**Garant****Boring bar stabiliser 7×D maxi, Type: 20R****Order data**

Order number	319469 20R
GTIN	4062406642525
Item class	31V

**Description****Version:**

Base body of high-quality tool steel, surface and functional faces hardened.

**Advantage:**

Reduces oscillation and vibration when used with all types of boring bars.

**Suitable for:**

All popular boring bars.

**Note:**

To determine the right type of boring bar stabiliser, it is essential to perform a collision check using the Hoffmann e-Tool data from the eShop or via the ToolScout! We recommend a maximum overhang length of 3×D of the types of boring bar used.

Maximum overhang, stabiliser incl. boring bar 10×D.

**Technical description**

C	1.5 mm
Cutting direction	right-hand
Radius R	1.2 mm
Ø D <sub>3</sub>	40 mm
Shank length L <sub>s</sub>	60 mm
Shank Ø D <sub>2</sub>	32 mm
Offset Z to the axis	20 mm
Clamping Ø D <sub>1</sub>	20 mm

Overall length $L_2$	206 mm
Overhang $L_1$	140 mm
Boring depth up to	$7 \times D$
Vibration	damped
Type of product	Boring bar stabiliser