

**Garant**
**HiPer-Drill base body, 12xD, Ø DC: 43mm**

**Order data**

Order number	231620 43
GTIN	4062406641771
Item class	21S

**Description**
**Version:**

- **Very high feed rates and maximum performance due to optimally matched geometries and materials.**
- **Precise positioning of the cutter insert due to Vee insert seating and secure clamping by the centre bore.**
- **High concentricity when assembled.**
- **Shank support for optimum stability in operation.**

Polished flutes.

**Application:**

For stationary and rotating use. For holes up to IT9 accuracy.

**Note:**

Further sizes up to Ø 50.99 mm available on request.

The insert screw must be replaced after every fifth change of cutter insert.

Reduce feed rates  $f$  by 10 % and  $v_c$  values by 40 %.

For process reliability when using the drill, initial pilot drilling to 1.5xD with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

Clamp in a hydraulic chuck (such as No. 302026 size 20) for optimum radial run-out.

For optimum stability, clamp the drill so the overhang is as short as possible.

For process reliability when using the drill, initial pilot drilling to 1.5xD with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

**Technical description**

Overall length L	670 mm
Dia. range $D_c$	43 - 44.99 mm

Series	HiPer-Drill
Reach L <sub>1</sub>	540 mm
Shank length L <sub>s</sub>	70 mm
Number of cutting edges Z	2
Clamping screw	231999 25IP
Shank Ø D <sub>s</sub>	40 mm
Version	12xD
Shank	ISO 9766
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling with oblique exit
Through-coolant	yes
Type of product	Indexable drill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 25IP	674252 25IP
Torx Plus® screw Drive 25IP	231999 25IP