



Cordless hammer drill / driver, Shank size: GSB1855



Order data

Order number	P07113 GSB1855
GTIN	4059952608358
Item class	03B

Description

Version:

- **Perfectly equipped for every application: Tools, batteries, charger and 100-piece Pick&Click accessories in an L-BOXX.**
- **Brushless cordless screwdriver. Robust and long-lasting thanks to EC motor, optimised 13 mm Röhmetal metal drill chuck and 2-speed all-metal gearbox for ideal force transfer when drilling and screwdriving.**
- **Ergonomic and modular. Compatible with the L-BOXX and integral accessories compartment in the cover for Pick&Click sets.**

Supplied with:

1× cordless drill/driver GSR 18V-55, 2× batteries 5.0 Ah, 1× charger GAL 18V-20, 100-piece accessories, L-CASE Pick&Click.

Technical description

Packaging	Modular case (L-Boxx)
Quick-clamping chuck range	13 mm
maximum torque soft	28 Nm
Weight without battery	5.39 kg
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion

Motor design	Brushless
maximum torque hard	55 Nm
Battery voltage	18 V
Battery capacity	5 Ah
Type of product	limpact drill /screwdriver