

Garant
Solid carbide milling cutter compacting cut, Diamond, Ø h10 DC: 4mm

Order data

Order number	209535 4
GTIN	4045197478344
Item class	11Y

Description
Version:

High performance geometry with multiple teeth for extremely high material removal rates in a single pass.

Left-hand helix, **compacting cut**. The material is pushed down on to the substrate. Highly suitable for thin materials.

Technical description

Cutting edge Ø D _c	4 mm
No. of teeth Z	8
Feed f _z for slot milling in graphite	0.03 mm
Corner chamfer width at 45°	0.08 mm
Feed f _z for slot milling in GRP CRP	0.03 mm
Shank Ø D _s	6 mm
Overall length L	60 mm
Flute length L _c	16 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA with h6
Tolerance nominal Ø	h10
Corner chamfer angle	45 degrees
Coating	Diamond

Tool material	Solid carbide
Standard	Manufacturer's standard
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	black
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
PVDF GF20	suitable	200 m/min	N
POM GF25	suitable	190 m/min	N
PA 66 GF30	suitable	170 m/min	N
PEEK GF30	suitable	150 m/min	N
PTFE CF25	suitable	180 m/min	N
PEEK CF30	suitable	160 m/min	N
Hybrids	suitable		
Honeycomb sandwich	suitable	350 m/min	N
GRP	suitable	190 m/min	N
GRP, CRP	suitable	190 m/min	N
Graphite	suitable	340 m/min	N
wet maximum	Suitable		
dry	Suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------