

Garant**Workpiece back-stop 3-dimensional, Type: 150****Order data**

Order number	360432 150
GTIN	4062406640439
Item class	31H

Description**Version:**

- **Stepless and quick adjustment.**
- **M8 mounting for T-nuts or direct mounting.**
- **Optional maximum extension 30 mm.**

Application:

For use on milling and drilling machines.

Material:

Anodised aluminium.

Optional extras:

T-nuts with M8 thread, see No. 370520 size 12 – 18.

Technical description

S axial spacing A	80 - 110 mm
suitable for colour code	TC
suitable for colour code	HiPo
suitable for colour code	LC

suitable for colour code	LC-GARANT
suitable for colour code	Duo
suitable for colour code	Duo Plus
suitable for colour code	T-Rex
suitable for colour code	Titan
suitable for colour code	Titan2/TitanSense
suitable for colour code	Basic
suitable for colour code	HD-Allmatic
suitable for colour code	Centro Gripp
suitable for colour code	NC8
suitable for colour code	LCV125G
suitable for colour code	HOLEX NC
Overall height	210 - 240 mm
Usable height N	145 - 175 mm
Type of product	Component backstop