

**rapid****Hose reel sheet metal reel, Type: 15SCS****Order data**

Order number	080076 15SCS
GTIN	4030704094049
Item class	08A

**Description****Version:**

Hose reels with **automatic pull-out and roll-up mechanism guided** by long life steel springs with **multiple stop points per revolution**.

Open hose reel in **painted, partially galvanised sheet steel design** with **variable run-out guide** and robust **rubber hose**. With patented SCS controlled automatic roll-up mechanism for avoidance of damage and injuries.

**Application:**

Suitable for air, water, oil, diesel.

For increased ergonomics by relieving cable tension, and for ensuring tidiness and for avoiding the risk of accidents and injuries due to hoses lying on the ground.

**Technical description**

Connection inlet	1/2 in
usable hose length	15 m
maximum operating pressure	50 bar
Connection outlet	1/2 in

Material of the housing	Sheet metal, painted
SCS automatic roll-up drum	yes
Body height	494 mm
Body depth	180 mm
Body width	470 mm
Type of product	Hose reel