




## Roughing end mill HSS-Co8, TiAlN, Ø js12 DC: 6mm



### Order data

Order number	192450 6
GTIN	4045197106209
Item class	12W

### Description

#### Version:

**Relief ground knuckle form profile.**

Centre cutting teeth for plunging.

**Universal end mills** for profile milling or for plunging.

Economy version.

#### Advantage:

Compared to multi-flute cutters, **better chip evacuation due to larger flutes.**

### Technical description

Corner chamfer width at 45°	0.3 mm
Cutting edge Ø D <sub>c</sub>	6 mm
Feed f <sub>z</sub> for slot milling in steel < 750 N/mm <sup>2</sup>	0.01 mm
No. of teeth Z	3
Shank Ø D <sub>s</sub>	6 mm
Overall length L	57 mm
Flute length L <sub>c</sub>	13 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 1835 B to h6
Tolerance nominal Ø	js12
Helix angle	25 degrees

Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	HSS Co 8
Standard	DIN 844 B
Milling profile	NR
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	78 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	55 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	55 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	17 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	14 m/min	M
GG(G)	suitable only under restricted conditions	46 m/min	K
CuZn	suitable only under restricted conditions	92 m/min	N
Uni	suitable		
wet maximum	suitable		