

**Garant**
**PCD slot drill with internal cooling straight cut, PCD, Ø h10 DC: 16mm**

**Order data**

Order number	209610 16
GTIN	4045197478078
Item class	11Y

**Description**
**Version:**

**High performance PCD slot drill** for the **highest demands in respect to material removal rates** when machining **GRP, CRP** and **graphite**.

**Axial angle 0°.**

Straight flutes for a neutral cut.

Through-coolant: yes

Tolerance nominal Ø: h10

No. of teeth Z: 2

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HA with h6

No. of teeth Z: 2

Flute length  $L_c$ : 20 mm

Overhang length  $L_1$  incl. recess: 30 mm

Recess Ø  $D_1$ : 15 mm

Overall length L: 125 mm

Shank Ø  $D_s$ : 16 mm

**Technical description**

Feed $f_z$ for slot milling in graphite	0.15 mm
Feed $f_z$ for slot milling in GRP CRP	0.1 mm
Cutting edge Ø $D_c$	16 mm
Corner chamfer width at 45°	0.1 mm
Recess Ø $D_1$	15 mm

Overhang length $L_1$ incl. recess	30 mm
No. of teeth Z	2
Shank $\varnothing D_s$	16 mm
Overall length L	125 mm
Flute length $L_c$	20 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA with h6
Tolerance nominal $\varnothing$	h10
Corner chamfer angle	45 °
Coating	PCD
Tool material	PCD
Standard	Manufacturer's standard
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	yes
Colour ring	black
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium	suitable	2400 m/min	N
Aluminium (short chipping)	suitable	2000 m/min	N
Alu > 10% Si	suitable	1500 m/min	N
PMMA acrylic	suitable	1000 m/min	N
PE-HD	suitable	900 m/min	N
PA 66	suitable	900 m/min	N
PEEK	suitable	800 m/min	N
PVDF GF20	suitable	1200 m/min	N
POM GF25	suitable	1200 m/min	N

PA 66 GF30	suitable	1000 m/min	N
PEEK GF30	suitable	1000 m/min	N
PTFE CF25	suitable	1000 m/min	N
PEEK CF30	suitable	800 m/min	N
Hybrids	suitable		
MMC	suitable	400 m/min	N
GRP	suitable	500 m/min	N
CRP	suitable	500 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	Suitable		
Air	suitable		
<b>Services</b>			

Shank clamping flats for shrink-fit chucks, with retainer function Shank Ø tool 16 mm

SZ2025 16

Shank grinding Type HB

129100 HB