

Deep pot magnet with toleranced dimensions, Neodymium, Ø: 20mm



Order data

Order number	085929 20
GTIN	2050001737625
Item class	08Q

Description

Version:

- **Shielded cylindrical magnets with 3 to 6 times the clamping force of hard ferrite magnets.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 80 °C.**
- **Magnetic core made of neodymium.**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

Material of the surface	Nickel
Nominal clamping force	280 N
Height	25 mm
Ø	20 mm
maximum temperature resistance	80 °C
maximum shortening dimension rear	6 mm
Material of the magnet core	Neodymium
Type of product	Cylindrical clamping magnet

