

Garant

Solid carbide torus cutter, TiAlN, Ø e8 DC / R1: 8/2,0mm



Order data

Order number	206300 8/2,0
GTIN	4045197124357
Item class	11X

Description

Version:

With **double relief ground side clearance angle**.

Tolerance: Corner radius $R_1 = \pm 0.005$ mm.

Application:

Especially for **high speed machining in mould and tool making for copy milling**. Excellent results when **milling dry**.

Note:

NEW GENERATION AVAILABLE!

Recommended successor product is No. 206335.

Technical description

Recess Ø D_1	7.4 mm
Corner radius R_1	2 mm
Overhang length L_1 incl. recess	54 mm
Feed f_z for copy milling in steel < 1100 N/mm ²	0.028 mm
Feed f_z for side milling in steel < 1100 N/mm ²	0.025 mm
Cutting edge Ø D_c	8 mm
No. of teeth Z	4
Shank Ø D_s	8 mm
Flute length L_c	9 mm
Overall length L	100 mm

Shank	DIN 6535 HA to h6
Helix angle	30 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	e8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.2×D for side milling
Through-coolant	no
Shank tolerance	h6
Colour ring	without
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 750 N/mm ²	suitable	140 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	35 m/min	H
INOX < 900 N/mm ²	suitable	80 m/min	M
GG(G)	suitable	90 m/min	K
wet maximum	Suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		

~~Air~~
Services

Suitable

Shank grinding Type HB

129100 HB