

Deep pot magnet with toleranced dimensions, SmCo₅, Ø: 16mm



Order data

Order number	085928 16
GTIN	2050000965173
Item class	08Q

Description

Version:

- **Shielded cylindrical magnets with 3 to 6 times the clamping force of hard ferrite magnets.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 200 °C.**
- **Magnetic core made of samarium-cobalt (SmCo₅).**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

maximum shortening dimension rear	2 mm
maximum temperature resistance	200 °C
Nominal clamping force	125 N
Height	20 mm
Material of the surface	Nickel
Ø	16 mm
Material of the magnet core	SmCo ₅
Type of product	Cylindrical clamping magnet

