

Garant
Solid carbide torus cutter HPC, TiAlN, Ø DC / R1: 2/0,2mm

Order data

Order number	206323 2/0,2
GTIN	4045197640819
Item class	11X

Description
Version:
GARANT Diabolo 70:

Special solid carbide substrate with extremely high tensile strength combined with **outstanding wear resistance** for optimum process reliability.

Newly developed **nano-crystalline high-tech coating for hard milling up to 70 HRC**. Very suitable for **continuous use** in tool and mould making.

Sizes 2 – 5: **Recess angle $\alpha = 15^\circ$** .

Tolerances:

- **Corner radius: $R_1 = \pm 0.01$ mm.**

Application:

Due to the **special hard geometry** ideal for use on hardened materials from 60 HRC to 70 HRC.

Technical description

Feed f_z for side milling in steel < 70 HRC	0.005 mm
Overhang length L_1 incl. recess	10 mm
Corner radius R_1	0.2 mm
Recess $\varnothing D_1$	1.9 mm
Cutting edge $\varnothing D_c$	2 mm
Feed f_z for copy milling in steel < 70 HRC	0.005 mm
No. of teeth Z	4
Shank $\varnothing D_s$	6 mm
Flute length L_c	2 mm

Overall length L	58 mm
Shank	DIN 6535 HA to h6
Helix angle	30 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	0 / -0.02
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.05×D for side milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	red
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 60 HRC	suitable only under restricted conditions	150 m/min	H
Steel < 65 HRC	suitable	110 m/min	H
Steel < 67 HRC	suitable	90 m/min	H
Steel < 70 HRC	suitable	80 m/min	H
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------

