

Garant
PCD slot drill with internal cooling compacting cut, PCD, Ø h10 DC: 6mm

Order data

Order number	209620 6
GTIN	4045197478139
Item class	11Y

Description
Version:

High performance PCD slot drill for the **highest demands in respect to material removal rates** when machining **GRP, CRP** and **graphite**. **Axial angle negative. $\alpha = -2^\circ$.**

Compacting cut.

The material is pushed down on to the substrate. Highly suitable for thin materials.

Through-coolant: yes

Tolerance nominal Ø: h10

No. of teeth Z: 2

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HA with h6

No. of teeth Z: 2

Flute length L_c : 15 mm

Overhang length L_1 incl. recess: 20 mm

Recess Ø D_1 : 5.4 mm

Overall length L: 60 mm

Shank Ø D_s : 6 mm

Technical description

Overhang length L_1 incl. recess	20 mm
Feed f_z for slot milling in GRP CRP	0.03 mm
Recess Ø D_1	5.4 mm
Cutting edge Ø D_c	6 mm
Corner chamfer width at 45°	0.1 mm
No. of teeth Z	2

Feed f_z for slot milling in graphite	0.1 mm
Shank $\varnothing D_s$	6 mm
Overall length L	60 mm
Flute length L_c	15 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA with h6
Tolerance nominal \varnothing	h10
Corner chamfer angle	45 °
Coating	PCD
Tool material	PCD
Standard	Manufacturer's standard
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	yes
Colour ring	black
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable	2400 m/min	N
Aluminium (short chipping)	suitable	2000 m/min	N
Alu > 10% Si	suitable	1500 m/min	N
PMMA acrylic	suitable	1000 m/min	N
PE-HD	suitable	900 m/min	N
PA 66	suitable	900 m/min	N
PEEK	suitable	800 m/min	N
PVDF GF20	suitable	1200 m/min	N
POM GF25	suitable	1200 m/min	N
PA 66 GF30	suitable	1000 m/min	N

PEEK GF30	suitable	1000 m/min	N
PTFE CF25	suitable	1000 m/min	N
PEEK CF30	suitable	800 m/min	N
Hybrids	suitable		
MMC	suitable	400 m/min	N
GRP	suitable	500 m/min	N
CRP	suitable	500 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	Suitable		
Air	suitable		

Services

Shank grinding Type HB

129100 HB