

Deep pot magnet with toleranced dimensions, SmCo₅, Ø: 25mm



Order data

Order number	085928 25
GTIN	2050000965180
Item class	08Q

Description

Version:

- **Shielded cylindrical magnets with 3 to 6 times the clamping force of hard ferrite magnets.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 200 °C.**
- **Magnetic core made of samarium-cobalt (SmCo₅).**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

maximum temperature resistance	200 °C
Material of the surface	Nickel
Nominal clamping force	400 N
Ø	25 mm
Height	35 mm
maximum shortening dimension rear	7 mm
Material of the magnet core	SmCo ₅
Type of product	Cylindrical clamping magnet

