



## Roughing end mill HSS-Co8, TiAlN, Ø DC: 30 mm



### Order data

Order number	192650 30
GTIN	4045197107688
Item class	12W

### Description

#### Version:

#### With relief ground knuckle form profile.

Up to size 20 with end cutting teeth profile for plunging.

The wide teeth lands permit multiple re-grinding without losing the profile.

Sizes 6M to 25M – **MID mills:** dimensions to **factory standard, which is between DIN 844 stub and DIN 844 long.**

Economy version.

Through-coolant: no

Tolerance nominal Ø: js12

No. of teeth Z: 5

Helix angle: 30 degrees

Direction of infeed: horizontal and oblique

Shank: DIN 1835 B to h6

No. of teeth Z: 5

Flute length  $L_c$ : 45 mm

Overall length L: 121 mm

Shank Ø  $D_s$ : 25 mm

Corner chamfer width at 45°: 0.7 mm

Feed  $f_z$  for slot milling in steel < 750 N/mm<sup>2</sup>: 0.031 mm

### Technical description

Cutting edge Ø $D_c$	30 mm
Corner chamfer width at 45°	0.7 mm
No. of teeth Z	5

Feed $f_z$ for slot milling in steel < 750 N/mm <sup>2</sup>	0.031 mm
Shank $\varnothing D_s$	25 mm
Overall length L	121 mm
Flute length $L_c$	45 mm
Direction of infeed	horizontal and oblique
Shank	DIN 1835 B to h6
Tolerance nominal $\varnothing$	js12
Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	HSS Co 8
Standard	DIN 844 B
Milling profile	NR
Through-coolant	no
Colour ring	without
Type of product	End mill