

Garant
Roughing end mill, TiAlN, Ø DC: 7mm

Order data

Order number	192840 7
GTIN	4045197108036
Item class	11W

Description
Version:
Relief ground fine pitch knuckle form profile.

Centre cutting teeth for plunging.

Technical description

Cutting edge Ø D _c	7 mm
Feed f _z for slot milling in steel < 900 N/mm ²	0.01 mm
No. of teeth Z	3
Corner chamfer width at 45°	0.3 mm
Shank Ø D _s	10 mm
Overall length L	66 mm
Flute length L _c	16 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 1835 B to h6
Tolerance nominal Ø	±0.12
Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	HSS Co 8

Standard	DIN 844
Milling profile	HR
Through-coolant	no
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm ²	suitable	78 m/min	P
Steel < 750 N/mm ²	suitable	55 m/min	P
Steel < 900 N/mm ²	suitable	55 m/min	P
Steel < 1100 N/mm ²	suitable	29 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	25 m/min	P
INOX < 900 N/mm ²	suitable	17 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	14 m/min	M
GG(G)	suitable only under restricted conditions	46 m/min	K
CuZn	suitable only under restricted conditions	92 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		