

Garant
Roughing end mill, TiAlN, Ø DC: 20mm

Order data

Order number	192840 20
GTIN	4045197108135
Item class	11W

Description
Version:
Relief ground fine pitch knuckle form profile.

Centre cutting teeth for plunging.

Technical description

No. of teeth Z	4
Feed f_z for slot milling in steel $< 900 \text{ N/mm}^2$	0.043 mm
Corner chamfer width at 45°	0.3 mm
Cutting edge $\varnothing D_c$	20 mm
Shank $\varnothing D_s$	20 mm
Overall length L	104 mm
Flute length L_c	38 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 1835 B to h6
Tolerance nominal \varnothing	± 0.12
Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	HSS Co 8

Standard	DIN 844
Milling profile	HR
Through-coolant	no
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm ²	suitable	78 m/min	P
Steel < 750 N/mm ²	suitable	55 m/min	P
Steel < 900 N/mm ²	suitable	55 m/min	P
Steel < 1100 N/mm ²	suitable	29 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	25 m/min	P
INOX < 900 N/mm ²	suitable	17 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	14 m/min	M
GG(G)	suitable only under restricted conditions	46 m/min	K
CuZn	suitable only under restricted conditions	92 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		