




Roughing end mill HSS-Co8, TiAlN, Ø DC: 10mm



Order data

Order number	192650 10
GTIN	4045197107503
Item class	12W

Description

Version:

With relief ground knuckle form profile.

Up to size 20 with end cutting teeth profile for plunging.

The wide teeth lands permit multiple re-grinding without losing the profile.

Sizes 6M to 25M – **MID mills:** dimensions to **factory standard, which is between DIN 844 stub and DIN 844 long.**

Economy version.

Through-coolant: no

Tolerance nominal Ø: js12

No. of teeth Z: 4

Helix angle: 30°

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 1835 B to h6

No. of teeth Z: 4

Flute length L_c : 22 mm

Overall length L: 72 mm

Shank Ø D_s : 10 mm

Corner chamfer width at 45°: 0.4 mm

Feed f_z for slot milling in steel < 750 N/mm²: 0.014 mm

Technical description

Feed f_z for slot milling in steel < 750 N/mm ²	0.014 mm
Cutting edge Ø D_c	10 mm
No. of teeth Z	4

Corner chamfer width at 45°	0.4 mm
Shank Ø D _s	10 mm
Overall length L	72 mm
Flute length L _c	22 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 1835 B to h6
Tolerance nominal Ø	js12
Helix angle	30 °
Corner chamfer angle	45 °
Coating	TiAlN
Tool material	HSS Co 8
Standard	DIN 844 B
Milling profile	NR
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm ²	suitable	78 m/min	P
Steel < 750 N/mm ²	suitable	55 m/min	P
Steel < 900 N/mm ²	suitable	55 m/min	P
Steel < 1100 N/mm ²	suitable	29 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	25 m/min	P
INOX < 900 N/mm ²	suitable	17 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	14 m/min	M

GG(G)	suitable only under restricted conditions	46 m/min	K
CuZn	suitable only under restricted conditions	92 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		