



## HOLEX Pro Steel solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 3,71-X



### Order data

Order number	122501 3,71-X
GTIN	4062406657345
Item class	12F

### Description

#### Version:

**Straight major cutting edges** and a **special flute profile** ensure a good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and an extremely wear-resistant coating.

Up to Ø 1.9 with 4 facets, from Ø 2 with relieved cone.

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Versions with HB and HE shank available at the same price as HA.

For **HB shanks**: use order **no. 122502**.

For **HE shanks**: use order **No. 122503**. Delivery time: 10 weeks

Minimum order quantity: 5 pieces

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by  $\pm 10\%$  (minimum 1 piece).

### Technical description

Flute length $L_c$	24 mm
Number of cutting edges Z	2
Standard	DIN 6537 K

Ø range	3.71 - 4.7 mm
Overall length L	66 mm
Shank Ø D <sub>s</sub>	6 mm
Tolerance nominal Ø	h7
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	105 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	85 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
Uni	suitable		

wet maximum	suitable
dry	suitable