


Garant
**GARANT Diabolo solid carbide torus cutter HPC, TiAlN, Ø e8 DC / R1:
12/1,0mm**

Order data

Order number	206322 12/1,0
GTIN	4045197598448
Item class	11X

Description
Version:
GARANT Diabolo:

Special geometry, coating and carbide, specially for hard machining.

Double relief ground side clearance angle.

Tolerance: Corner radius $R_1 = \pm 0.005 \text{ mm}$.

Technical description

Corner radius R_1	1 mm
Feed f_z for copy milling in steel < 65 HRC	0.08 mm
Overhang length L_1 incl. recess	38 mm
No. of teeth Z	4
Feed f_z for side milling in steel < 65 HRC	0.08 mm
Cutting edge $\varnothing D_c$	12 mm
Recess $\varnothing D_1$	11 mm
Shank $\varnothing D_s$	12 mm
Flute length L_c	12 mm
Overall length L	83 mm
Shank	DIN 6535 HA to h6
Helix angle	30 degrees

Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	e8
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.2×D for side milling
Cutting width a_e for milling operation	0.05×D for copy milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	red
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	200 m/min	P
Steel < 50 HRC	suitable	190 m/min	H
Steel < 55 HRC	suitable	170 m/min	H
Steel < 60 HRC	suitable	150 m/min	H
Steel < 65 HRC	suitable	110 m/min	H
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB

129100 HB