



## Cordless nutrunner, right angle, Type: CLBA083



### Order data

Order number	071142 CLBA083
GTIN	697099651482
Item class	03S

### Description

#### Version:

The cordless Cleco® CellClutch™ assembly tools are smart yet simple to use, and bring programming functionality to the assembly line along with a classic counting function. Precision and repetition accuracy with a CMK value  $> 1.67$  (at a tolerance of  $\pm 10\%$  in conjunction with ISO 5393).

- **Easy to program: Program speeds and multi-stage screw tightening procedures to avoid errors and improve productivity.**
- **Tried-and-tested Cleco clutch: For reliability and a long service life in the production line.**
- **Operator status light: Colour display for screw tightening and batch counting status.**
- **Multi-colour LED: Work light for additional "OK/NOK" user feedback whilst also illuminating your workpiece.**
- **Programmable screwdriving strategies: Eliminate damage to the thread and errors when screwdriving thanks to programmable speeds and strategies.**
- **Uniform battery platform.**

#### Supplied with:

Without batteries and without charger.

#### Note:

You can find suitable batteries and chargers under No. 073827 size MB18; 073816 size MB18 and under No. 073840. A pre-setting device is necessary for setting the torque; these can be found from No. 654381.

## Technical description

Height	76 mm
Speed range	92 - 915 min <sup>-1</sup>
Number of rechargeable batteries contained	0
Tool arbor drive profile	Square
Length	452.4 mm
Tool arbor size	3/8 in
Battery voltage	18 V
Power supply	Rechargeable battery-powered
Battery capacity	3 Ah
Torque range	2.2 - 8 Nm
Weight without battery	1.46 kg
Type of product	Screwdriver