



Cordless nutrunner, right angle, Type: CLBA203



Order data

| | |
|--------------|----------------|
| Order number | 071142 CLBA203 |
| GTIN | 697099651505 |
| Item class | 03S |

Description

Version:

The cordless Cleco® CellClutch™ assembly tools are smart yet simple to use, and bring programming functionality to the assembly line along with a classic counting function. Precision and repetition accuracy with a CMK value > 1.67 (at a tolerance of $\pm 10\%$ in conjunction with ISO 5393).

- **Easy to program: Program speeds and multi-stage screw tightening procedures to avoid errors and improve productivity.**
- **Tried-and-tested Cleco clutch: For reliability and a long service life in the production line.**
- **Operator status light: Colour display for screw tightening and batch counting status.**
- **Multi-colour LED: Work light for additional "OK/NOK" user feedback whilst also illuminating your workpiece.**
- **Programmable screwdriving strategies: Eliminate damage to the thread and errors when screwdriving thanks to programmable speeds and strategies.**
- **Uniform battery platform.**

Supplied with:

Without batteries and without charger.

Note:

You can find suitable batteries and chargers under No. 073827 size MB18; 073816 size MB18 and under No. 073840. A pre-setting device is necessary for setting the torque; these can be found from No. 654381.

Technical description

| | |
|--|------------------------------|
| Power supply | Rechargeable battery-powered |
| Tool arbor size | 3/8 in |
| Battery capacity | 3 Ah |
| Battery voltage | 18 V |
| Height | 76 mm |
| Length | 492 mm |
| Tool arbor drive profile | Square |
| Number of rechargeable batteries contained | 0 |
| Speed range | 36 - 360 min ⁻¹ |
| Torque range | 8.3 - 21 Nm |
| Weight without battery | 1.73 kg |
| Type of product | Screwdriver |