

Garant
End cutting thread mill 2xD, TiAlN, G: G1/2

Order data

Order number	139523 G1/2
GTIN	4062406653767
Item class	11J

Description
Version:

Tool for **combined production** of bore, chamfer and thread **in a single work step**. Pre-drilling is no longer required. The innovative centre cutting edge geometry makes this tool a specialist in thread production in **hardened and hard-to-machine materials**. The **TiAlN high-performance coating** ensures the longest possible **tool life**, especially in hardened steels **up to 63 HRC**. All tools have left-hand cutting and are suitable for **right-hand and left-hand threads**.

Application:

For **Whitworth parallel pipe threads** DIN-ISO 228/1 (threads that do not form a seal within the connections).

Note:

Always use with cooling lubricant emulsion. (Fat content min 8%). In the case of steels **>45 HRC** can only be used with **compressed air!** Also suitable for thread dimensions **G5/8 to G3/4**.

Technical description

Cutting edge $\varnothing D_c$	15.7 mm
Shank length L_s	51.2 mm
Overhang L_1	47 mm
Feed f_z in steel < 65 HRC	0.01 mm
Number of clamping slots	4
Shank $\varnothing D_s$	16 mm
Overall length L	100 mm

Thread depth	47
Neck Ø D ₁	12.92 mm
Thread pitch	1.814 mm
Programming radius	7.85 mm
Cutter length l _c	6 mm
Thread size	G1/2
Threads per inch	14
Through-coolant	yes
Coating	TiAlN
Thread type	G
Thread type	BSP
Flank angle	55 degrees
Tool material	Solid carbide
Shank	DIN 6535 HA with h6
Number of cutting edges Z	4
Application for type of drilling	up to 2×D for through holes
Application for type of drilling	up to 2×D for blind holes
Countersink angle	90 degrees
Cutting direction	left-hand
Shank tolerance	h6
Internal/external application	Internal
Type of product	Combination drill / thread mill

User data

	Suitability	V _c	ISO code
Steel < 1100 N/mm ²	suitable	90 m/min	P
Steel < 1400 N/mm ²	suitable	90 m/min	P
Steel < 55 HRC	suitable	45 m/min	H
Steel < 60 HRC	suitable	40 m/min	H

Steel < 65 HRC	suitable only under restricted conditions	35 m/min	H
INOX < 900 N/mm ²	suitable	60 m/min	M
INOX > 900 N/mm ²	suitable	60 m/min	M
Ti > 850 N/mm ²	suitable	45 m/min	S
wet maximum	suitable		
Air Services	suitable		

Shank grinding Type HB	129100 HB
Shank grinding Type HE	129100 HE